

IOTRONTM pH / ORP / ISE Measurement Product Lines

Connection Diagram of Iotron™ Sensors with 1054A Preamplifiers to New Uniloc 1054A Transmitters

Cable Color Coding	Instrument Terminal Name	Uniloc Terminal Number
Black	mV in	1
Green	+ 5 VDC	3
White	RTD in	5
Shield	Ground (RTD)	6
Red	Ground	7

Note 1: This sensor has been tested under laboratory conditions using a uniloc 1054A transmitter. This transmitter is prone to noise under industrial conditions. If such a condition exists, please connect terminal 1 and the instrument ground via a 0.02 microFarad/50V capacitor. This should completely quiet the reading on the transmitter.

Note 2: Keep the sensor body beyond the thread or receptacle dry all the time.