

## Connection Diagram of Iotron™ Sensors without Preamplifiers to Mettler Toledo 2100e pH Analyzers (Revision 3)

### Connection from Iotron™ Sensor to Terminal Block in Mettler Toledo Transmitter

<u>Iotron™</u> <u>Cable Color Coding</u>	<u>Mettler Toledo</u> <u>Instrument Terminal Name</u>	<u>Mettler Toledo</u> <u>Terminal Number</u>
Clear	Signal Input (Measure)	1
Red	Reference	2
Black	TC Input	D
Black	TC Input	E

Note 1: The temperature compensator is 1000 Ohm Pt RTD

Note 2: Terminals 2 & 3 and C & D must be jumpered.

