


Connection Diagram of Iotron™ Sensors without Preamplifiers and without solution ground to Mettler Toledo pH M300 Analyzers

Connection from Iotron™ Sensor to TB3 Terminal Block in Mettler Toledo Transmitter

<u>Iotron™</u> <u>Cable Color Coding</u>	<u>Mettler Toledo</u> <u>Instrument Terminal Name</u>	<u>Mettler Toledo</u> <u>Terminal Number</u>
Clear	Signal Input (Measure)	1
Red	Reference	3
White	TC Input	6
Green	TC Input	8

Note 1: The temperature compensator is 1000 Ohm Platinum

Note 2: Terminals 3 & 4 and must be jumpered together.



Last Revised 05-20-09